

NEO MPI 3222

FIBOX

Enclosing innovations



Sample image

Order symbol: NEO MPI 3222

Product nbr: 4850070

Description: Multiperforated plastic mounting plate

Remarks:

Including: Plastic mountingplate

EAN: 6418074314796

EI. number:

- Finland: 3424424
- Denmark: 8212098158
- Sweden: 2506228

Dimensions:	Height	Width	Depth
mm:	280	180	3
inch:	11.02	7.09	0.12

Materials:

Material:	ABS
Base colour:	
Cover colour:	
Gasket material:	

Temperatures:

Temperature °C (short term):	
Temperature °C (continuous):	
Temperature °F (short term):	
Temperature °F (continuous):	

Rating:

Ingress protection (EN 60529):	
Impact Resistance (EN 62262):	
Electrical insulation:	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	-
Flammability Rating:	
Glow Wire Test (IEC 695-2-1) °C:	C
NEMA Class	

Certificates: