



## NMBT WC24

WIRE CUTTER, BATTERY OPERATED MAX D=24mm, 18V 2.0Ah Li-Ion BATTERY

NMBT WC24 is a battery-powered cable and wire cable tool. The tool is equipped with a battery gauge and the head is rotatable 180°. Comes with one battery, one battery charger and a shoulder strap/harness in a durable plastic case.

Can cut the following: Wire 6 x 7, 18 mm Wire 6 x 12, 24 mm Wire 6 x 19, 24 mm CU cable, 24 mm AL cable, 24 mm

Can not be used for piano wire.

Battery: 18 VDC, 2.0 Ah Li-Ion Pressure: 78 kN Weight: 6.0 kg

Dimensions case (LxWxH): 560x160x400 mm

## Product Properties:

Isolation protection 1000 V	No
With spring	N/A

## Dimensions:

Unit	pcs
Max. cutting diameter	24 mm
Weight	6 kg
Length cutting blade	24 mm
Length	500 mm
MOQ	1 .

## Approvals:

Isolation protection 1000 V	No
-----------------------------	----

## Compliance:

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (223 Subs. Jan 2022)

## Other information:

<b>Trademark</b>	NEMIQ
<b>ETIM-Class</b>	EC003421 - Steel wire mesh cutter
<b>ETIM-Release</b>	7.0
<b>Product Group</b>	Battery tools
<b>Search Description</b>	BMNOVALL, BMNOVNEW
<b>Alternative SKU</b>	NMBTWC24
<b>Warranty</b>	1 years

**Logistic information:**

<b>Barcode</b>	733117610393
<b>Country of origin</b>	TW
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>Stock code</b>	NMBT WC24
<b>Taric code</b>	84622910
<b>Unit</b>	pcs
<b>MOQ</b>	1 .