



NP 695

Indent crimp tool for cable lugs, splices and uninsulated DIN terminals. Stepless settings of crimping dies depending on cable series and area of cable lug.

Standard scale for:

KS / KR	6.0 mm ²
KSF / KRF	10-70 mm ²
KST / KRT	10-95 mm ²
KSD / KRD	16-95 mm ²
DIN 46234	6.0-70 mm ²

Built-in ratchet and release button. Completed crimps with settings according to scale on tool will fulfill SS-EN 61238-1.

Length: 525 mm.

With locking device (for mechanical tools)	Yes
Inserts exchangeable	No
With automatic return	Yes
Suitable for	Cable lugs and connectors
Construction/operation	Mechanical
Compression shape	Arbour clamping
Number of included inserts	1 .
Cycle time	2 s

Product Description	Stock code
PRESSVERKTYG RÖRKABELSKOR, 6-95mm ² , KR, KRF, KRT, KRD & DIN 46234	NP 695