



NR-33KS

Order No.: 16.0650

EUR 67,90

RRP *

PRODUCTINFOS

Weatherproof horn speaker

- IP66 tested, protected against powerful water jets
- 8 Ω speaker system
- Suitable for general indoor and outdoor applications
- Robust plastic housing
- Mounting bracket and screws made of stainless steel

TECHNICAL SPECIFICATIONS

NR-33KS

Active/passive	passive
Impedance	8 Ω
Frequency range	275-7,000 Hz

NR-33KS

Number of speakers	1
Power rating	12 W
Peak music power output	25 W
Sensitivity	106 dB/W/m
Radiation angle, horizontal	100°
Radiation angle, vertical	50°
Housing material	plastic
Colour	light grey
Mounting facility	stainless steel mounting bracket
Protective class	IP66
Admiss. ambient temp.	-20 °C to +50 °C
Width	250 mm
Height	145 mm
Depth	272 mm
Weight	1.5 kg
Replacement voice coil	IT-230/VC
Other features	weatherproof

* **Important Notice:** The retail prices shown here are non-binding recommendations that retailers can charge their customers. They are not part of any specific offer or advertisement. These prices include all charges as well as VAT, but do not cover any additional delivery and shipping costs. Our latest price lists for the retail market include all applicable delivery and payment terms for retailers.