



NSCT 0560

E1661967

CABLE CUTTER 1-HANDED WITH STRIPPING BLADE 0.3-6.0mm², MAX D=6mm, RETURN SPRING

One hand cable cutter for cutting and stripping 0.3-6.0 mm², AWG 24-10. Handle with return spring. Strip depth adjustment controls.
Length: 140 mm

Product Properties:

Insulated	Yes
Suitable for solid cores	Yes
Suitable for stranded conductors	Yes
Suitable for fine strand conductors	Yes
Grip design	1-component
With impact protection	No
Suitable for steel wire braiding	Yes
Replaceable cutting head	No
Cutting jaws exchangeable	No
With strip function	Yes
Construction/operation	Mechanic one hand
Isolation protection 1000 V	No
With spring	Yes

Dimensions:

Unit	pcs
Max. cable cross section	0.3-6 mm ²
Suitable for max. cable diameter	6 mm
Total length	140 mm

MOQ 1 .

Approvals:

VDE tested	No
Isolation protection 1000 V	No

Compliance:

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (223 Subs. Jan 2022)

Other information:

Trademark	NEMIQ
ETIM-Class	EC000142 - Cable shears
ETIM-Release	7.0
Product Group	1-hand
Search Description	E1620440, SCT001
Alternative SKU	NSCT0560

Logistic information:

Barcode	733117611079
E-no	E1661967
Country of origin	TW
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	NSCT 0560
Taric code	82032000
Unit	pcs
MOQ	1 .