

# Product data sheet

Specifications



Earth braids section 6mm<sup>2</sup>, length 150mm, eyebolt 7mm. Packaging unit: 10.

NSYEB156D6

## Main

Range	Spacial
Anwendung	Multi-purpose
Product or component type	Earthing braid
Device composition	1 braid
Quantity per set	Set of 10

## Complementary

Material	Tinned copper
Fixing mode	Nut and washer - on earth connection location
Length	150 mm
Width	12 mm
Nominal cross section	6 mm <sup>2</sup>
Diameter	7 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	12.0 g
Package 1 Height	0.5 cm
Package 1 width	12 cm
Package 1 Length	22 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

---

<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

---

### **Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---