

Product data sheet

Specifications



Earth braids section 25mm²,
length 200mm, eyelet hole 6,4mm.
Packaging unit: 10.

NSYEB2025D8

Main

Range	Spacial
Anwendung	Multi-purpose
Product or component type	Earthing braid
Device composition	1 braid
Quantity per set	Set of 10

Complementary

Material	Tinned copper
Fixing mode	Nut and washer - on earth connection location
Length	200 mm
Width	27 mm
Nominal cross section	25 mm ²
Diameter	8.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	55.0 g
Package 1 Height	0.5 cm
Package 1 width	2 cm
Package 1 Length	22 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	554.0 g
Package 2 Height	3 cm
Package 2 width	2 cm
Package 2 Length	22 cm

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
-----------------	-----------