

# Product data sheet

Specifications



Earth leads section 6mm<sup>2</sup>, length 130mm, eyelet hole 6,4mm.  
Packaging unit: 10.



NSYEL136D6

## Main

Range	Spacial
Anwendung	Multi-purpose
Product or component type	Earthing wire
Device composition	1 lead
Quantity per set	Set of 10

## Complementary

Material	PVC (polyvinyl chloride) green and yellow for sheath Brass and copper alloy for terminal
Fixing mode	Nut and washer - on earth connection location
Length	130 mm
Width	10 mm
Nominal cross section	6 mm <sup>2</sup>
Diameter	6.4 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	11.0 g
Package 1 Height	1 cm
Package 1 width	1 cm
Package 1 Length	13 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

---

<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

---

### **Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---