

Product data sheet

Specifications



Earth leads section 6mm², length 160mm, eyelet hole 6,4mm.
Packaging unit: 10.



NSYEL166D6

Main

Range	Spacial
Anwendung	Multi-purpose
Product or component type	Earthing wire
Device composition	1 lead
Quantity per set	Set of 10

Complementary

Material	PVC (polyvinyl chloride) green and yellow for sheath Brass and copper alloy for terminal
Fixing mode	Nut and washer - on earth connection location
Length	160 mm
Width	10 mm
Nominal cross section	6 mm ²
Diameter	6.4 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	13.0 g
Package 1 Height	20 cm
Package 1 width	10.5 cm
Package 1 Length	1 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Weight	150.0 kg
Package 2 Height	10.5 cm
Package 2 width	1 cm
Package 2 Length	10 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------