

Acer Chromebook 311

(C722-K56B)



- Processor: MediaTek Octa-Core ARM Cortex A73/A53 (MT8183)
- Display: 11.6" HD (non-glare)
- Memory: 4 GB LPDDR4X RAM
- Mass storage: 32 GB eMMC
- Graphics card: Mali-G72 MP3 GPL
- Operating System: Google Chrome OS







Acer C722-K56B **SPECIFICATIONS**







Ordering Information

Series Acer Chromebook 311 C722-K56B Model name Part number NX.A6UEG.001 EAN 4710886480037 Short description

11.6" HD (non-glare) / MediaTek Octa-Core ARM Cortex A73/A53 (MT8183) / 4 GB LPDDR4X RAM / 32 GB eMMC / Mali-G72 MP3 GPU / Google Chrome OS / Black

Operating System

Operating System Google Chrome OS

Housing

Housing / Color Black Component door

Dimensions 296 x 206 x 21.1 mm (W x D x H)

1.17 kg Weight Passively cooled (fanless) Yes

Display

Display size 11.6 inches (29.46 cm) Display type

Acer ComfyView™ HD Display with LED-

Backlight (non-glare)

Display resolution in pixel 1366 x 768 Aspect ratio 16:9

Processor and chipset

MediaTek Octa-Core ARM Cortex A73/A53 Processor Processor (MT8183)

Clock frequency 2.0 GHz

Cache

Processing cores / threads

Chipset Integrated SOC

Storage and drives

Memory Memory configuration

1x 4 GB LPDDR4X RAM (onboard) Maximum RAM Onboard-Memory (not exchange- or

4 GB I PDDR4X RAM

upgradeable) 32 GB eMMC Mass storage

Optical drive

Graphics card

Graphics card Mali-G72 MP3 GPU

LAN

Wireless LAN 802.11ac/a/b/g/n, 2,4 GHz & 5 GHz, 2x2 MU-MIMO

Wireless WAN / SIM-Card -/, Wireless Gigabit

Bluetooth Bluetooth 4.2 NFC

IO ports

HDMI VGA

Displayport Thunderbolt USB 3.1

USB 3.1 1x (Type-C Gen. 1)

USB 3.0 USB 2.0 1x Ethernet (RJ-45) Cardreader

Audio port 1x headphone/speaker jack

Docking port

Keyboard Acer FineTip keyboard (74-/75-/78-keys)

Keyboard layout German (QWERTZ) Backlit keyboard

Multi-Gesture Touchpad Touchpad



Acer C722-K56B SPECIFICATIONS

Security

Fingerprint sensor

TPM TPM Modul
Kensington Lock Yes
Security software -

Audio and video

Audio High Definition audio support
Speaker Two built-in stereo speakers
Microphone Built-in microphone
Webcam HD webcam

Battery and power adapter

Battery Li-lon Battery (4 cells / 3220 mAh / 48 Wh)

Battery lifetime Up to 15 hours
Power adapter 45W AC-Power

Power adapter 45W AC-Power-Adapter (USB Type C Adapter)

Battery built in Yes

Warranty

Warranty 2 years pickup and return