

SDI Cable with BNC rearTWIST



NX0628BTGN*-BL

Assembled coaxial cable, 0.6/2.8 AF FRNC-C (ZNK CT2850202), halogen-free, flame retardant, digital video SDI, overall Ø 4.5 mm (Attu@100MHz/100m = 10.5 dB), green, with 2x BNC rearTWIST [NBNC75BFG7](#), black boots, other colored boots available on request.

Order Numbers

NX0628BTGN0.5BL = 0.5 meters
NX0628BTGN1-BL = 1 meter
NX0628BTGN2.5BL = 2.5 meters
NX0628BTGN5-BL = 5 meters
NX0628BTGN7.5BL = 7.5 meters
NX0628BTGN10-BL = 10 meters
NX0628BTGN15-BL = 15 meters
NX0628BTGN20-BL = 20 meters