

SDI Cable with BNC rearTWIST, FLEX



NX06L28BTBL*-BL

Black, highly flexible coaxial cable 0.6L/2.8 AF (ZNK CT2739600), digital video SDI, (Attu.@100MHz/100 m = 12.1dB), with an outer diameter of 4.5 mm, PVC jacket and 2x BNC rearTWIST male cable connectors NBNC75BFG7 with black bushings. Other coloured bushings are available on request.

Order Numbers

NX06L28BTBL0.3-BL = 30 cm
NX06L28BTBL0.5-BL = 50 cm
NX06L28BTBL1-BL = 1 meter
NX06L28BTBL2.5-BL = 2.5 meters
NX06L28BTBL5-BL = 5 meters
NX06L28BTBL7.5-BL = 7.5 meters
NX06L28BTBL10-BL = 10 meters
NX06L28BTBL15-BL = 15 meters
NX06L28BTBL20-BL = 20 meters