

SDI Cable with BNC rearTWIST, FLEX



NX08L37BTBL*-BL

Black, highly flexible coaxial cable 0.8L/3.7 DZ (ZNK CT2850500), HDTV 5GHz, with an outer diameter of 5.9 mm, PVC jacket and 2x BNC rearTWIST male cable connectors [NBNC75BLP9](#) with black bushings. Other coloured bushings are available on request.

Order Numbers

NX08L37BTBL03BL = 0.3 meters

NX08L37BTBL05BL = 0.5 meters

NX08L37BTBL1-BL = 1 meter

NX08L37BTBL2.5-BL = 2.5 meters

NX08L37BTBL5-BL = 5 meters

NX08L37BTBL7.5-BL = 7.5 meters

NX08L37BTBL10BL = 10 meters

NX08L37BTBL15-BL = 15 meters

NX08L37BTBL20BL = 20 meters

NX08L37BTBL30-BL = 30 meters

NX08L37BTBL40-BL = 40 meters