

RF-Cable, 50 Ohm, RG58



NXRG58BTBL*-BL

Assembled Coaxial Cable RF RG58 B/U MIL C17 D (ZNK CK2771699), black, overall \varnothing 5 mm (Attu @ 100M Hz/100 m = 16.3 dB), with 2x NBNC-RG58, male 50 Ω (Ohm), black boots.

Order Numbers

NXRG58BTBL0.5-BL = 0.5 meters

NXRG58BTBL1-BL = 1 meter

NXRG58BTBL2.5-BL = 2.5 meters

NXRG58BTBL5-BL = 5 meters

NXRG58BTBL7.5-BL = 7.5 meters

NXRG58BTBL10-BL = 10 meters

NXRG58BTBL15-BL = 15 meters

NXRG58BTBL20-BL = 20 meters