

# Analog Cable with BNC rearTwist

---



## NXRG59BTBL\*-BL

---

Assembled coaxial cable RG59 B/U MIL C17, flexible, analog video, outer diameter 6.2 mm (Attu.@100MHz/100m = 11.5dB), black, with 2x BNC rearTWIST [NBNC75BLP7](#), black boots, colored boots available on request.

## Order Numbers

---

NXRG59BTBL0.5BL = 0.5 meters

NXRG59BTBL1-BL = 1 meter

NXRG59BTBL2.5BL = 2.5 meters

NXRG59BTBL5-BL = 5 meters

NXRG59BTBL7.5BL = 7.5 meters

NXRG59BTBL10-BL = 10 meters

NXRG59BTBL15-BL = 15 meters

NXRG59BTBL20-BL = 20 meters

NXRG59BTBL30-BL = 30 meters