

CCTV Security Camera | Dome | HD | For use with analogue HD DVR

General information

Compose a CCTV installation which matches all your needs, securing your home thoroughly and efficiently. Connect this Nedis® HD dome camera to your analogue HD DVR to capture sharp images no matter the conditions. Its metal housing is waterproof (IP66) which provides you with all the freedom to mount this camera either inside your home or outdoors. Equipped with infrared array LEDs. These bundle the light, covering a longer distance.

Features

- HD 720p
- Night vision up to 20 m
- Waterproof IP66

Specifications

Lens:	3,6 mm
LED:	2
Viewing angle:	63 °
Input Voltage:	12 VDC
Image chip:	1/4" CMOS
Operating temperature:	-10 - 50 °C
Night vision:	20 m
Max. resolution:	720P
Cable length:	50 cm
IP rating:	IP66
Camera design:	Dome
Colour:	White
Usage:	Indoor and Outdoor
Interface:	DC
Interface:	BNC
Features:	Metal
Features:	Night Vision
Features:	Robust and Impact-Resistant



Sales information

Order code:	AHDCDW10WT
Product description:	CCTV Security Camera Dome HD For use with analogue HD DVR
Packaging:	Giftbox
Brand name:	Nedis



Quantity	LxWxH (mm)	Weight
1	110x120x114	357 gr.
24	460x350x280	9308 gr.



CCTV Security Camera | Dome | HD | For use with analogue HD DVR

Package contents

Security camera
Installation materials