

CCTV Security Camera | Dome | Full HD | For use with analogue HD DVR

General information

Compose a CCTV installation which matches all your needs, securing your home thoroughly and efficiently.

Connect this Nedis® varifocal Full HD bullet camera to a Nedis® analogue HD DVR and capture sharp images no matter the conditions. The camera features 4x zoom and focus which can be adjusted to optimise recordings to meet your specific requirements.

Its metal housing is waterproof (IP66) which provides you with all the freedom to mount this camera either inside your home or outdoors. Equipped with infrared array LEDs. These bundle the light, covering a longer distance.

Features

- Full HD 1080p
- Night vision up to 30 m
- Waterproof IP66
- 4x zoom

Specifications

Lens:	2,8 - 12 mm
LED:	3
Viewing angle:	33 - 96 °
Input Voltage:	12 VDC
Image chip:	1/3" CMOS
Operating temperature:	-10 - 50 °C
Zoom:	4
Night vision:	30 m
Max. resolution:	1080P
Cable length:	50 cm
IP rating:	IP66
Camera design:	Dome
Colour:	White
Usage:	Indoor and Outdoor
Interface:	DC



Sales information

Order code:	AHDCDW20WT
Product description:	CCTV Security Camera Dome Full HD For use with analogue HD DVR
Packaging:	Giftbox
Brand name:	Nedis



Quantity	LxWxH (mm)	Weight
1	141x125x137	731 gr.
18	445x444x271	14042 gr.



CCTV Security Camera | Dome | Full HD | For use with analogue HD DVR

Interface:	BNC
Features:	Metal
Features:	Night Vision
Features:	Robust and Impact-Resistant
Features:	Zoom-Function

Package contents

Security camera
Installation materials