

Bluetooth 4.0 Micro USB Dongle | Software Included | USB

General information

This Micro Bluetooth dongle connects your PC wirelessly to mobile devices such as mobile phones, tablets and headsets. Installation is only a matter of Plug & Play. This dongle has a range up to 100 metre, supports Bluetooth voice data, and is ideal to use in combination with a notebook thanks to the very small design and low energy usage. The supplied CSR Harmony software is easy to use and can be used for a variety of functions, such as data upload and download from, for instance, your smartphone, tablet or notebook.

Features

- Individual MAC address for every single model
- Chipset: CSR 8510A10 (with aptX)

Specifications

Power rating:	5 V 0.5 A
Bluetooth version:	v4.0
Device type:	USB-Adapter
Transfer speed:	3 Mbps
Colour:	Black
Material:	Plastic / Metal
dBi:	2 dBi
Usage:	Notebook
Usage:	PC
Connection:	USB
Connection:	Bluetooth

Package contents



Sales information

Order code: **BLDO100V4BK**
 Product description: Bluetooth 4.0 Micro USB Dongle |
 Software Included | USB
 Packaging: Blister
 Brand name: Nedis



Quantity	LxWxH (mm)	Weight
1	99x148x18	28 gr.
40	250x170x220	1300 gr.
160	480x390x280	5820 gr.



Bluetooth 4.0 Micro USB Dongle | Software Included | USB

Dongle
CSR Harmony software
Quick start guide