

HDMI - DVI Cable | HDMI™ Connector - DVI-D 24+1-Pin Male | 2.0 m | Anthracite

General information

Cable to connect a monitor to a PC. 10.2 Gbps high-speed transmission capacity, supporting 720P / 1080i / 1080P full HD resolution with a bandwidth support 165MHz.

Features

Specifications

- 24 ct gold-plated contacts for an outstanding image quality
- Full copper conductor to ensure superior transmission properties
- Metal-braided shielding to reduce electromagnetic interference
- Durable moulded connectors specifically designed for intensive usage

Connector design - side B: Straight 7.3 mm Diameter: AWG value: 30 Plating: Gold Max. resolution: 1920x1080 Connector design - side A: Straight 2.00 m Length: Cable design: Round Outside material: PVC Packaging: Polybag Conductor material: Copper Colour: Anthracite Cable type: High Speed HDMI with Ethernet Connection B: DVI-D 24+1-Pin Male

HDMI Connector

Package contents

Connection A:



Sales information

Order code: CCBP34800AT20

Product HDMI - DVI Cable | HDMI™ Connector - DVIdescription: D 24+1-Pin Male | 2.0 m | Anthracite

Brand name: Nedis



| Quantity | LxWxH (mm) | Weight |
|----------|---------------------------|---------------------|
| 1 | 220x25x220 315x305x410 | 140 gr. |
| 40 | 315x305x410 | 140 gr. 7960 gr. |



HDMI - DVI Cable | HDMI™ Connector - DVI-D 24+1-Pin Male | 2.0 m | Anthracite

DVI - HDMI™ Cable