

USB 2.0 Cable | A Male - Micro B Male | 3.0 m | Anthracite

General information

Cable to connect a smartphone or tablet to a PC to enable sync and charge.

Features

- 24 ct gold-plated contacts for reliable data transmission
- USB 2.0 technology for high-speed data transmission up to 480 Mbps
- Full copper conductors for error-free signal flow
- Durable moulded connectors specifically designed for intensive usage

Specifications

Connector design - side B:	Straight
Max. speed:	480 Mbps
Diameter:	4.5 mm
AWG value:	28 / 24
Plating:	Gold
Connector design - side A:	Straight
Length:	3.00 m
Cable design:	Round
Outside material:	PVC
Packaging:	Polybag
Conductor material:	Copper
Colour:	Anthracite
Cable type:	USB 2.0
Connection B:	Micro B Male
Connection A:	USB-A Male

Package contents

USB 2.0 cable



Sales information

Order code:	CCBP60500AT30
Product description:	USB 2.0 Cable A Male - Micro B Male 3.0 m Anthracite
Packaging:	Polybag
Brand name:	Nedis



Quantity	LxWxH (mm)	Weight
1	145x20x230	78 gr.
5	245x99x159	481 gr.
20	266x220x346	1994 gr.