

## USB 3.0 Cable | A Male - A Female | 2.0 m | Blue

### General information

This cable is suitable for extending a USB cable.

### Features

- Durable connector for a firm connection
- Copper cores for a reliable data transmission
- Supports transfer rates up to USB SuperSpeed (5 GB/s)

### Specifications

Connector design - side B:	Straight
Max. speed:	4.8 Gbps
AWG value:	28 / 24
Diameter:	5.5 mm
Plating:	Nickel
Cable design:	Round
Colour:	Blue
Connector design - side A:	Straight
Length:	2.00 m
Outside material:	PVC
Packaging:	Polybag
Conductor material:	Copper
Cable type:	USB 3.0
Connection B:	USB A Female
Connection A:	USB-A Male

### Package contents

1x USB 3.0 Cable



### Sales information

Order code: **CCGP61010BU20**  
 Product description: USB 3.0 Cable | A Male - A Female | 2.0 m | Blue  
 Packaging: Polybag  
 Brand name: Nedis



5 412810 1275175

Quantity	LxWxH (mm)	Weight
1	150x230x20	97 gr.
100	510x320x390	10683 gr.