# USB 3.0 Cable | A Male - Micro B Male | 2.0 m | Blue

## General information

This cable is suitable for connecting a device to a computer.

## Features

- Durable connector for a firm connection
- Copper cores for a reliable data transmission
- Supports transfer rates up to USB SuperSpeed (5 GB/s)

## Specifications

| | |
|---|---|
| Connector design - side B: | Straight |
| Max. speed: | 4.8 Gbps |
| AWG value: | 28 / 24 |
| Diameter: | 5.5 mm |
| Plating: | Nickel |
| Cable design: | Round |
| Colour: | Blue |
| Connector design - side A: | Straight |
| Length: | 2.00 m |
| Outside material: | PVC |
| Packaging: | Polybag |
| Conductor material: | Copper |
| Cable type: | USB 3.0 |
| Connection B: | Micro B Male |
| Connection A: | USB-A Male |

## Package contents

1x USB 3.0 Cable



## Sales information

| | |
|---|---|
| Order code: | **CCGP61500BU20** |
| Product description: | USB 3.0 Cable \| A Male - Micro B Male \| 2.0 m \| Blue |
| Packaging: | Polybag |
| Brand name: | Nedis |

5 412810 275236

| Quantity | LxWxH (mm) | Weight |
|---|---|---|
| 1 | 150x230x20 | 97 gr. |
| 100 | 510x320x390 | 10780 gr. |

Information is subject to change without prior notice. Contents may differ from what is shown. Supplier can not be held responsible, nor liable for the information contained in this document. This document was generated at 09/01/2019 13:00:26