

USB 3.0 Cable | Type-C Male - A Female | 0.15 m | Black

General information

Connect multiple devices to your PC or MacBook with this USB C 2.0 cable to experience the ultimate all-in-one connectivity solution. The cable supports OTG (On The Go) so you can connect your mobile device to a USB device without having to use a normal computer.. Perfectly suitable for charging and fast data transfer.

Features

- USB C for the ultimate all-in-one solution: sync, charge and AV support
- Suitable for connecting multiple devices to your PC or MacBook
- User-friendly connector which connects in any direction
- USB 2.0 for fast data transfer of 480 Mbps
- Hybrid connectivity solution suitable for any brand
- Supports OTG (On The Go)

Specifications

Connector design - side B:	Straight
Max. speed:	4.8 Gbps
AWG value:	32 / 24
Diameter:	3.8 mm
Plating:	Nickel
Connector design - side A:	Straight
Length:	0.15 m
Outside material:	PVC
Packaging:	Polybag
Conductor material:	Copper
Colour:	Black
Cable type:	USB 3.0
Connection B:	USB A Female
Connection A:	USB-C™ Male



Sales information

Order code:	CCGP61710BK02
Product description:	USB 3.0 Cable Type-C Male - A Female 0.15 m Black
Packaging:	Polybag
Brand name:	Nedis



Quantity	LxWxH (mm)	Weight
1	80x230x20	30 gr.
100	420x180x240	3273 gr.
200	440x380x260	6505 gr.



USB 3.0 Cable | Type-C Male - A Female | 0.15 m | Black

Package contents

1x USB-C™ 3.0 Adapter Cable