

## IP Security Camera | 1280x720 | Panorama | White / Black

### General information

Secure your home discretely with this Nedis® HD panorama camera.

The camera is equipped with a fisheye lens. This enables a 180° panoramic view covering the entire room, which means that the camera in itself does not move.

This, together with a compact design, ensures dedicated low-key camera observation.

Perfect to keep an eye on your children, for example.

Receiving notifications, viewing both live and recorded footage and zooming in for a more detailed image all work via a free app on your smartphone.

Images are also recorded 24/7 to a MicroSD card so you never have to miss a thing.

### Features

- Compact design / zooming in via smartphone for low-key observation
- 24/7 recordings stored on MicroSD card (up to 128 GB)
- Motion detection with notifications
- 180° fisheye lens for 100% panoramic coverage of a room

### Specifications

Lens:	1.44 mm
LED:	2
Viewing angle:	180 °
Input Voltage:	5 VDC
Image chip:	1/4" CMOS
Operating temperature:	0-40 °C
Megapixel:	1 MPixel
Night vision:	5 m
Max. radio transmit power:	20 dBm
Antenna gain:	2 dBi
Frequency range:	2412 - 2472 MHz
Accessories:	Adapter



### Sales information

Order code: **IPCMP10CWT**  
 Product description: IP Security Camera | 1280x720 |  
 Panorama | White / Black  
 Packaging: Giftbox with eurolock  
 Brand name: Nedis



Quantity	LxWxH (mm)	Weight
1	98x165x50	324 gr.
40	415x365x280	13556 gr.



## IP Security Camera | 1280x720 | Panorama | White / Black

Accessories:	Camera Mount
Accessories:	USB-Cable
App available for:	Android™
App available for:	iOS
Max. resolution:	1280x720
Colour:	White/Black
Wireless technology:	Wi-Fi
Interface:	SD
Interface:	USB (Micro)
Storage type:	microSD
Power plug:	Euro / Type C (CEE 7/16)
Features:	Night Vision
Features:	2-Way Audio
Features:	Easy to Install

### Package contents

HD panorama camera  
Camera mount  
USB power adapter  
USB cable  
Installation materials  
Manual