

## Uninterruptible Power Supply | 650 VA | 360W | 2 Sockets

### General information

Protect your computer and files against power-failures and surges with the powerful 650VA UPS. During a power failure, the battery will give you 10 minutes to save your files and shut down the computers correctly. With the monitoring software installed, you can manage the UPS and see the status on your computer screen.

### Specifications

Height:	142 mm
Battery recharge time:	360 min
Width:	100 mm
Operating time:	10 min
LCD display:	No
Output Current:	650 VA
Output power:	360 W
No. of batteries:	1
Colour:	Black
Technology:	Sealed Lead Acid
Number of sockets:	2
Output voltage:	230 VDC
Voltage:	AC 100 - 240 V
Length:	287 mm
Power plug:	Schuko / Type F (CEE 7/7)
Socket type:	Protective Contact
Socket type:	RJ11

### Package contents

UPS  
Software CD  
USB cable  
Manual



### Sales information

Order code: **UPSD650VBK**  
 Product description: Uninterruptible Power Supply | 650 VA | 360W | 2 Sockets  
 Packaging: Giftbox  
 Brand name: Nedis



Quantity	LxWxH (mm)	Weight
1	330x220x140	4263 gr.
4	350x240x590	17902 gr.