

## WiFi Smart IP Camera | Pan/Tilt | HD 720p

### General information

An essential addition to any smart home system, this Nedis® Smart Home IP Camera offers pan and tilt functionality to cover the whole room.

This wireless-controlled security camera connects directly with your home Wi-Fi network - no additional hub required - to be triggered by any motion and sound in the room.

#### Smart IP Camera

Home automation just got simpler. This easy to use camera can be easily connected to your existing Wi-Fi network to monitor rooms for any sound or motion.

It records in HD resolution (1280x720 pixels) for complete clarity of the images captured. In addition, the camera is just as powerful at night: with its night vision mode offering a range of 10.0 m.

The camera supports microSD cards of up to 128 GB (not included) to offer plenty of footage storage and its stylish and compact design means it can be placed anywhere within your room to record a viewing angle of 110° when its 1/4" CMOS sensor is triggered.

The pan and tilt functionality allow the camera to record a larger area when you control it by your phone or tablet.

#### About Nedis®SmartLife

Discover a wide and ever-expanding range of products - such as bulbs, switches, sockets, sensors, and cameras - that can all be controlled through an easy-to-use and intuitive app.

Whether you're looking for a single smart bulb or camera, or you want to automate your entire house, discover how accessible smart technology is today.

### Features

- Smart IP Camera - responds automatically to record any motion or sound in your room
- HD resolution - for crystal-clear footage capture



### Sales information

Order code:	<b>WIFICI20CGY</b>
Product description:	WiFi Smart IP Camera   Pan/Tilt   HD 720p
Packaging:	Giftbox with eurolock
Brand name:	Nedis



Quantity	LxWxH (mm)	Weight
1	190x94x90	215 gr.
20	405x210x435	8440 gr.

## WiFi Smart IP Camera | Pan/Tilt | HD 720p

- Easy to connect directly into your Wi-Fi network - no separate hub required
- Two-way communication - to hear and speak to those in the room
- Wall and ceiling mount included - easy to affix straight from the box
- Fully supported by all other products in the Nedis® SmartLife range.

### Specifications

Lens:	2.6 mm
LED:	1
Input Voltage:	5 VDC
Image chip:	1/4" CMOS
Operating temperature:	-20 - 50 °C
Max. radio transmit power:	18.5 dBm
Antenna gain:	3 dBi
Frequency range:	2.400 - 2.4832 GHz
Night vision:	10 m
Viewing angle:	110 °
Megapixel:	1 MPixel
Accessories:	Camera Mount
Accessories:	AC Adapter EU Plug
Accessories:	Self-Adhesive Pad
Accessories:	USB-Cable
App available for:	Android™ & iOS
Compatible with:	Nedis® SmartLife
Max. resolution:	720P
Colour:	Grey/White
Material:	Plastic
Wireless technology:	Wi-Fi
Interface:	USB (Micro)
Storage type:	microSD
Power plug:	Euro / Type C (CEE 7/16)
Features:	2-Way Audio
Features:	Night Vision
Features:	Motion Sensor
Features:	Pan Tilt Zoom

## WiFi Smart IP Camera | Pan/Tilt | HD 720p

### Package contents

- IP camera
- Alternative coloured cover
- USB cable
- Power adapter
- Camera mount
- Adhesive pad
- Quick start guide