



## DERAY SET 1000

KRYMPSLANGSSORTIMENT UTAN LIM, 2:1, 87 DELAR, L=70 & 200mm, BLANDADE FÄRGER, TUNN-V

Sortiment med 70 och 200 mm långa krympslangslängder i färgerna svart, röd, blå, vit och gul. Totalt 87 längder. Ø före Ø efter krympning 2.4 / 1.2 mm 3.2 / 1.6 mm 4.8 / 2.4 mm 6.4 / 3.2 mm 9.4 / 4.8 mm 12.7 / 6.4 mm 19.0 / 9.5 mm Temperaturområde: -55 grader C till + 125 grader C Krymptemperatur: från 120 grader C till 200 grader C Krympförhållande: 2:1 Genomslagshållfastighet: 20 kV/mm

## Product Properties:

Model	Thin-walled
Type	Heat-shrink
Shrink rate	2:1
With inner glue	No
Colour	Multi-coloured
Material	Polyolefin (PO-X)
Halogen free	No
Packaging	Assortment
Operating temperature	-55-125 °C

## Dimensions:

Unit	pcs
Inner diameter before heat-shrink	19 mm
Inner diameter after heat-shrink	1.2 mm
MOQ	1 .

## Approvals:

UL approval	No
-------------	----

## Environmental information:

## Logistic information:

<b>Barcode</b>	733117615970
<b>Country of origin</b>	CN
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>Packaging</b>	Assortment
<b>Stock code</b>	DERAY SET 1000
<b>Taric code</b>	39173200
<b>Unit</b>	pcs
<b>MOQ</b>	1 .