

Netac flash drives can be widely used in computers, in-vehicle devices, game consoles and other devices that have a USB interface and are compatible with this product. It can easily realize data backup, storage and transmission.

UM1 flash drive

64GB

128GB

256GB



• Unique shape design

Highlights

- Full metal shell, sturdy and durable.
- With lanyard hole at bottom.
- Non-slip surface design, high speed and stability.

Product Specification	
Interface	USB3.2
Dimension(mm)	36*12.2*4.6mm
Net Weight(g)	About 5.6g
Housing material	Zinc alloy
Standard color	Pearl nickel
Data transfer rate write(MB/s)	8-45MB/s
Data transfer rate read(MB/s)	100-160MB/s
operating temperature (°C)	0-60°C
Storage temperature (°C)	-20-70°C
Operation System	Windows 7/8 /10+ ;Mac OS X 10.5 +; Linux 2.6.x or +;
Max Working Voltage(V)/Current(mA)	V=5V/A=150mA
Warranty period	5 years

Netac

Netac Technology Co., Ltd.

Address: 16.18.19F, Netac, Building, Number 6 High-tech South St, Nanshan District, Shenzhen, P.R.China 518057

Tel: 86-755-26727516

E-mail: marketing@netac.com

Web: www.netac.com