

Product OD-W02WB-12PD


based LEDs WB & BPE W2x4.6d color white


| product-catalog | Based LEDs |
|----------------------------|---------------|
| color | white |
| part no. | OD-W02WB-12PD |
| voltage [V] | 12-14 |
| current [mA] | 13-16 |
| chromaticity coordinates | x 0.31/y 0.32 |
| operating temperature [°C] | -25 +60 |
| storage temperature [°C] | -30 +80 |
| | |

| chip construction | GaN |
|-------------------------------|--------------|
| luminous intensity typ. [mcd] | 750 at 15 mA |



- all dimension are in millimeter
- \bullet tolerance is \pm 0.25 mm unless otherwise noted
- specifications are subject to change whithout notice
- version 1.0





© OSHINO LAMPS GmbH, Tennenloher Straße 19, D 90425 Nürnberg