



213355
OGWTI-80G3-T4
Frame light barrier

Technical data (typ.)	+20°C, 24 V DC
Resolution	Ø 1,5 mm (dynamic), Ø 2,0 mm (static)
Sensitivity adjustment	Keypad
Display	LED Green - Status, yellow - Switching output 1, white - static/dynamic, yellow/red - Switching output 2 / Warning
Response time	0,05 ms
Release time	0,05 ... 10.000 ms
Ambient temperature during operation	-10 ... +60 °C
Protection type	IP 67
Connection	Connector, M8, 4-pin
Connection cable	TK ... /4
More information / accessories	https://www.di-soric.com/213355