

# **PRODUCT DATASHEET**

# SUBSTITUBE LED T8 STARTER



#### **AREAS OF APPLICATION**

- Not suitable for operation with electronic control gears

#### **PRODUCT BENEFITS**

- Extremely break resistant thanks to cover made of polycarbonate
- Mercury-free and RoHS compliant

#### **PRODUCT FEATURES**


- Substitute starter for the replacement of a fluorescent lamp with a LED tube
- Suitable for operation with low loss or conventional control gear or line voltage
- Integrated electrical fuse



## **TECHNICAL DATA**

Product weight	5.00 g
Order reference	SUBSTITUBE LED

# Graphics and application images



## **LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075013674	FS	46 mm x 25 mm x 42 mm	0.01 q	0.05dm³
	2		J	
4058075013681 VS 20	VS	99 mm x 32 mm x 218 mm	0.17g	0.69dm³
	20			
4058075013698	VS5	446 mm x 309 mm x 246 mm	7.42g	33.90dm³
	840			

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.