

# **PRODUCT DATASHEET**HALOSTAR STARLITE 5 W 12 V G4

HALOSTAR STARLITE 2000 | Low-voltage halogen lamps with pin base



#### **AREAS OF APPLICATION**

- General illumination
- Entrance lighting
- Accent lighting
- Lighting for reading
- Garden lighting
- Shops
- Restaurants, hotels and similar prestigious applications
- Offices, public buildings
- Outdoor applications only in suitable luminaires

#### **PRODUCT BENEFITS**

- Brilliant accent light
- Incredibly small dimensions for revolutionary new luminaire designs
- Approved for use in open luminaires (to IEC 60598-1)
- Axial filament for optimum directional light
- Special pins for corrosion protection
- UV filter
- Contains no mercury

#### **PRODUCT FEATURES**

- Average life: 2,000 h
- 100 % dimmable
- Color rendering index R<sub>a</sub>: 100

## **TECHNICAL DATA**

## Electrical data

Nominal wattage	5.00 W
Nominal voltage	12 V
Rated wattage	5.00 W
Power factor λ	1.00
Claimed equiv. conventional lamp power	5 W


#### Photometrical data

Nominal luminous flux	55 lm
Rated color temperature	2700 K
Light color (designation)	Warm White
Rated luminous flux	55 lm
Color rendering index Ra	100
Color temperature	2700 K
Luminous flux	55 lm
Color rendering index Ra	100

## Light technical data

Starting time	0.0 s
Warm-up time (60 %)	0.00 s

## Dimensions & weight



Diameter	10.0 mm
Overall length	33.0 mm
Light center length (LCL)	22.0 mm
Outer bulb	T10
Length	33.0 mm

## Lifespan

Nominal lamp life time	2000 h
Rated lamp life time	2000 h
Number of switching cycles	50000

#### Additional product data

Base (standard designation)	G4
Mercury content	0.0 mg
Mercury-free	Yes

## Capabilities


Burning position	Any
Dimmable	Yes

#### Certificates & standards

Energy consumption	6 kWh/1000h
Energy efficiency class	В

## Country-specific categorizations

## Light Distribution



Spectral power distribution

#### **LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075094154	Folding carton box 1	25 mm x 23 mm x 70 mm	3.10 g	0.04 dm <sup>3</sup>
4058075094161	Shipping carton box 40	144 mm x 107 mm x 121 mm	165.00 g	1.86 dm <sup>3</sup>
4058075103610	Unpacked 1	- x - x -	1.00 g	
4058075103627	Shipping carton box 5000	410 mm x 310 mm x 435 mm	7875.00 g	55.29 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.