

PRODUCT DATASHEETP CLAS A 75 8 W/4000K E27

PARATHOM Retrofit CLASSIC A | LED lamps, classic bulb shape



AREAS OF APPLICATION

- Perfect for decorative installations
- Domestic applications
- General illumination
- Outdoor use in outdoor luminaires only (minimum IP65)

PRODUCT BENEFITS

- Lamps with innovative LED "filament" technology
- Design, dimensions, luminous flux comparable to an incandescent or halogen lamp
- Very low energy consumption
- No UV and near-IR radiation in the light beam
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs
- Lower thermal output (compared with the standard reference product)

PRODUCT FEATURES

- Professional LED lamps for line voltage
- Beam angle: up to 300°
- Not dimmable
- Base: E27
- Mercury-free lamps



- Lifetime: up to 15,000 h

TECHNICAL DATA

Electrical data

Rated wattage	8.00 W
Nominal wattage	8.00 W
Nominal voltage	220240 V
Max. lamp no. on circuit break. 10 A (B)	81
Max. lamp no. on circuit break. 16 A (B)	131
Operating frequency	5060 Hz
Power factor λ	0.50
Claimed equiv. conventional lamp power	75 W


Photometrical data

Nominal luminous flux	1055 lm
Rated luminous flux	1055 lm
Rated color temperature	4000 K
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Cool White
Color temperature	4000 K
Luminous flux	1055 lm
Color rendering index Ra	≥80
Standard deviation of color matching	≤6 sdcm

Light technical data

Warm-up time (60 %)	0.50 s
Starting time	0.5 s

Dimensions & weight



Overall length	105.0 mm
----------------	----------

Diameter	60.0 mm
Outer bulb	A60
Length	105.0 mm

Temperatures & operating conditions

Maximum temperature at tc test point	62 °C
--------------------------------------	-------

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen maintenance at end of service life	0.70

Additional product data

Base (standard designation)	E27		
Mercury content	0.0 mg		
Mercury-free	Yes		
Design / version	Frosted		
Show WEEE picto	Yes		
Product remark	All technical parameters apply to the entire lampDue to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value		

Capabilities

Dimmable	No
----------	----

Certificates & standards

Energy efficiency class	A++
Energy consumption	8 kWh/1000h

Country-specific categorizations

ILCOS	DRAA/F-8/840-220-240-E27-60
Order reference	LEDPCLA75 8W/84

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075287563	Folding carton box 1	60 mm x 60 mm x 111 mm	48.00 g	0.40 dm³

4058075287570	Shipping carton box 10	325 mm x 136 mm x 126 mm	573.00 g	5.57 dm³
4058075808379	Folding carton box 1	60 mm x 60 mm x 111 mm	44.00 g	0.40 dm ³
4058075203907	Bundle 2	61 mm x 121 mm x 111 mm	93.00 g	0.82 dm ³
4058075203914	Shipping carton box 10	325 mm x 136 mm x 126 mm	558.00 g	5.57 dm ³
4058075809802	Shipping carton box 10	325 mm x 136 mm x 126 mm	651.00 g	5.57 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.