

# **PRODUCT DATASHEET**LEDinestra 25 200° 3.5 W/2700K S14s

# **LEDinestra | Tubular LED lamps**



#### **AREAS OF APPLICATION**

- Ideal for mirror lighting
- Hotels, restaurants
- Domestic applications
- Outdoor applications only in suitable luminaires

#### **PRODUCT BENEFITS**

- Long lifetime of up to 15,000 h
- Low energy consumption
- Good color rendering

#### PRODUCT FEATURES

- LED alternative to tubular incandescent lamps
- Uniform illumination
- Mercury-free lamps
- Made in Germany



## **TECHNICAL DATA**

# Electrical data

Rated wattage	3.50 W
Nominal wattage	3.50 W
Nominal voltage	220240 V
Operating frequency	5060 Hz
Claimed equiv. conventional lamp power	25 W

#### Photometrical data

Rated color temperature	2700 К
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 К
Luminous flux	260 lm
Color rendering index Ra	80
Nominal luminous flux	260 lm

## Dimensions & weight



Overall length	300.0 mm
Temperatures & operating conditions	
Maximum temperature at tc test point	55 °C
Lifespan	
Nominal lamp life time	15000 h
Rated lamp life time	15000 h

Additional product data

Base (standard designation)	S14s
Mercury-free	Yes

## Capabilities

<b>Dimmable</b> No	
--------------------	--


#### Certificates & standards

Energy efficiency class	A+
-------------------------	----

#### Country-specific categorizations

ILCOS	DRL/F-3,5/827-230-S14S-29/300
Order reference	LEDINESTRA25 3,

## **Light Distribution**



## Spectral power distribution

#### **LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075817739	Folding carton box 1	33 mm x 50 mm x 307 mm	110.00 g	0.51 dm <sup>3</sup>
4058075817746	Shipping carton box 10	370 mm x 215 mm x 155 mm	1301.00 g	12.33 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## **REFERENCES / LINKS**

For further products and actual information concerning LED lamps see

www.ledvance.com/ledlamps

For Guarantee see

www.ledvance.com/guarantee

#### **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.