



Universal AC Power Adapter 3 / 4.5 / 5 / 6 / 7.5 / 9 / 12 VDC

0.6 A

General information

Very compact and super efficient universal 600 mA plug-in adapter with 3-12 V output and LED indicator. The 6 exchangeable power tips make this adapter very suitable for many devices.

Specifications		
Output current:	600 mA	
Output voltage selection:	Manually	
Output Current:	0.6 A	
Output plug type:	2.5 x 2.1 mm	
Output plug type:	3.5 x 2.1 mm	
Output plug type:	5.0 x 2.1 mm	
Output plug type:	5.5 x 2.5 mm	
Output plug type:	3.5 x 1.35 mm	
Output plug type:	5.5 x 1.5 mm	
Cable length:	1.80 m	
Output power:	7.2 W	
Voltage:	AC 100 - 240 V	
Usage:	Universal	
Power plug:	Euro / Type C (CEE 7/16)	
Output voltage:	3 VDC	
Output voltage:	4.5 VDC	
Output voltage:	5 VDC	
Output voltage:	6 VDC	
Output voltage:	7.5 VDC	
Output voltage:	9 VDC	
Output voltage:	12 VDC	

Package contents

- Adapter
- 6 interchangeable connectors
- Manual



Sales information

Order code: P.SUP.EU600

Product description: Universal AC Power Adapter 3 / 4.5 / 5 /

6 / 7.5 / 9 / 12 VDC 0.6 A

Packaging: Giftbox Brand name: HQ



Quantity	LxWxH (mm)	Weight
1	45x80x85 105x230x405 230x250x420	112 gr. 2995 gr. 6280 gr.
25	105x230x405	2995 gr.
50	230x250x420	6280 gr.