



Universal AC Power Adapter 3 / 4.5 / 6 / 7.5 / 9 / 12 VDC 0.7 A - 1.5 A

General information

Very compact and super efficient universal 1500 mA plug-in adapter with 6 selectable voltages between 3 and 12 Volt output. The adapter has a load, current and heat protection. The 8 exchangeable power tips make this adapter very suitable for many devices.

Supplied with 8 detachable plugs

6,3x3 - 5,5x2,5 - 5,5x2,1 - 5x2,1 - 4,95x1,98 - 4x1,7 - 3,5x1,35 - 3,5x1

Specifications

Output current:	700 mA - 1500 mA
Output voltage selection:	Manually
Output Current:	0.7 A - 1.5 A
Output plug type:	mono jack 2.5mm
Output plug type:	mono jack 3.5mm
Output plug type:	DC plug 3.0 x 1.0 mm
Output plug type:	DC plug 5.0 x 2.1 mm
Output plug type:	DC plug 3.5 x 1.35 mm
Output plug type:	DC plug 4.0 x 1.7 mm
Output plug type:	DC plug 2.35 x 0.7 mm
Output plug type:	DC plug 5.5 x 2.5 mm
Output power:	7.5 W
Cable length:	1.80 m
Voltage:	AC 100 - 240 V
Usage:	Universal
Power plug:	Euro / Type C (CEE 7/16)
Output voltage:	3 VDC
Output voltage:	4.5 VDC
Output voltage:	6 VDC
Output voltage:	7.5 VDC
Output voltage:	9 VDC
Output voltage:	12 VDC



Sales information

Order code:	P.SUP.SMP1-BL
Product description:	Universal AC Power Adapter 3 / 4.5 / 6 / 7.5 / 9 / 12 VDC 0.7 A - 1.5 A
Packaging:	Blister
Brand name:	HQ



5 412810 017157

Quantity	LxWxH (mm)	Weight
1	145x60x170	191 gr.
10	155x355x295	2085 gr.
30	315x375x470	6860 gr.