


KEMET Part Number: PME271E547MR19T0
(P277QS473M300L)

PME271E/P277, Film, Metallized Paper, Safety, 0.047 uF, 20%, 300 VAC (X1), 630 VDC, 110°C, Lead Spacing = 15.2mm



Dimensions	
L	18.5mm MAX
H	14.3mm MAX
T	8.5mm MAX
S	15.2mm +/-0.4mm
H0	18.5mm +/-0.5mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	350

General Information	
Series:	PME271E/P277
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Safety Class:	X1
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
THB Performance:	No
Construction:	Molded
Component Weight:	3.42 g
Miscellaneous:	SRF= 6.4 MHz.

Specifications	
Capacitance:	0.047 uF
Capacitance Tolerance:	20%
Voltage AC:	300 VAC (X1)
Voltage DC:	630 VDC
Temperature Range:	-40/+110°C
Rated Temperature:	110°C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	1200 V/us