

Operating temperature

P / Q - type

Trip Temperature (C°) ± Tolerance (°C)	Reset Temperature (°C) ± Tolerance (°C)	Differential (°C) average
40±5	30 +10/-5	10
45±5	30 +10/-5	15
50±5	35 +10/-5	15
55±5	40 +10/-5	15
60±5	40 +10/-5	20
65±5	40 ±10	25
70±5	40±10	25
75±5	45±10	30
80±5	50±10	30
85±5	50±10	35
90±5	55±10	35
95±5	60±10	35
100±5	60±10	40
105±5	65±10	40
110±5	65±10	45
115±5	70±10	45
120±5	70±10	50
125±5	75±10	50
130±10	80±10	50
135±10	80±10	55
140±10	85±10	55
145±10	90±10	55
150±10	90±10	60

other differential or reset temperature are available on enquiry

RS TECHNICAL DATA

DIESE INFORMATION IST EIN
 AUSZUG AUS DATENBUECHERN
 RS-COMPONENTS UEBERNIMMT FUER
 DIE RICHTIGKEIT KEINE HAFTUNG


Limitor GmbH

Mühlstr. 88
 73547 Lorch Waldhausen

17.10.02