

Digital multimeters & Pen type multimeters

PAN 118

Digital multimeter 600V CAT III with NCV

- Non contact voltage test (NCV)
- Single-pole phase tester
- Digital Display 14 mm
- Backlight
- Auto range
- LED flashlight
- Diode test
- Data Hold
- Auto power off

Scope of delivery: Operating manual, test leads



Technical Data	PAN 118
DC voltage (V =)	0,1 mV - 600 V
AC voltage (V ~)	1 mV - 600 V
DC current (A =)	0,1 μ A - 200 mA
AC current (A ~)	0,1 μ A - 200 mA
Resistance (Ω)	0,1 Ω - 20 M Ω
Continuity test (•)))	< 50 Ω
Accuracy (%)	0,5 % - 2,0 %
Dimensions	130 x 62 x 27 mm
Weight (gross / net)	147 / 243 g
Required battery(s):	2x 1,5V AAA
Measuring category (CAT)	CAT III 600 V



PAN 118 Video DE:



PAN 118 Video EN:

