

Multifunction meters

PAN LAN1

2 in 1 LAN Tester & Multimeter 300V CAT III auto range

- Digital Display 21 mm
- Diode test
- Data Hold
- **Maximum value memory**
- **LAN test for continuity, open, short and swapped leads (RJ45, RJ11, BNC)**
- Auto power off
- **Auto range**
- Continuous test function

Scope of delivery: Operating manual, test leads, protective cover



Technical Data	PAN LAN1
DC voltage (V =)	0,1 mV - 600 V
AC voltage (V ~)	10 mV - 600 V
DC current (A =)	0,1 μ A - 200 mA
AC current (A ~)	0,1 μ A - 200 mA
Resistance (Ω)	0,1 Ω - 20 M Ω
Continuity test (•)))	< 150 Ω
Accuracy (%)	0,5 % - 2 %
Dimensions	162 x 74,5 x 44 mm
Weight (gross / net)	750 / 245 g
Required battery(s):	1x 9V 6LR61 + 2 x 1,5 V AAA
Measuring category (CAT)	CAT II 600 V / CAT III 300 V



PAN LAN1 Video DE:



PAN LAN1 Video EN:

