

PB 8192 RB

Screwdrivers for Pozidriv screws acc. to DIN ISO 8764-1, colour-coded according to handle size

Destornillador para tornillos Pozidriv según DIN ISO 8764-1, con codificación de tamaños por colores



PB 8192.0-60 LG		0	1,6-2	4	60	140	23	10		7 610733 254064
PB 8192.1-80 YG		1	2,5-3	5	80	175	44	10		7 610733 254071
PB 8192.2-100 OR		2	3-5	6	100	205	72	10		7 610733 254088
PB 8192.3-150 BL		3	6-8	8	150	270	143	10		7 610733 254095

PB 8192

Screwdrivers for Pozidriv screws, tip according to DIN ISO 8764-1 Main sizes printed in bold-faced letters

Destornillador en cruz Pozidriv, punta conforme a DIN ISO 8764-1 Dimensiones principales impresas en negrita



PB 8192.0-60	0	1,6-2	4	60	140	23	10		7 610733 079032
PB 8192.1-80	1	2,5-3	5	80	175	44	10		7 610733 079049
PB 8192.1-130	1	2,5-3	5	130	225	51	10		7 610733 216857
PB 8192.2-100	2	3-5	6	100	205	72	10		7 610733 079056
PB 8192.2-150	2	3-5	6	150	255	83	10		7 610733 216864
PB 8192.2-300	2	3-5	6	300	405	117	10		7 610733 216871
PB 8192.3-150	3	6-8	8	150	270	146	10		7 610733 079063
PB 8192.4-200	4	8-10	10	200	330	221	10		7 610733 216888

PB 8192 S

Screwdrivers for Pozidriv screws, tip according to DIN ISO 8764-1, with hexagon portion

Destornillador en cruz Pozidriv, punta conforme a DIN ISO 8764-1, con extremo hexagonal



PB 8192.S 2-100	2	3-5	7	100	210	10	101	10	7 610733 079070
PB 8192.S 3-150	3	6-8	8	150	270	13	157	10	7 610733 079087
PB 8192.S 4-200	4	8-10	10	200	320	17	247	10	7 610733 079094

PB 8200

Socket wrenches with SwissGrip handle

Llave de vaso con mango, para tornillos hexagonales, mango SwissGrip



PB 8200.4-70	2	70	150	26	10	7 610733 068470
PB 8200.4,5-80	2,2	80	170	34	10	7 610733 068487
PB 8200.5-85	2,5	85	180	45	10	7 610733 068494
PB 8200.5,5-90	3	90	190	54	10	7 610733 068500
PB 8200.6-90	3,5	90	195	74	10	7 610733 068517
PB 8200.7-100	4	100	205	77	10	7 610733 068524