


PB 304 Combined engineer's hammer and soft mallet
 Dead-blow, handle made of USA hickory wood, FSC approved
 Cushioning the recoil by weights in the mallet body
 - allows full and precise strikes


Martillo combinado de bola con cabeza plástica antirebote
 mango Hickory (EE.UU.), con homologación FSC
 Amortiguación del rebote mediante lastres en la cabeza del martillo
 - golpes fuertes y precisos



	Ø						
PB 304.1	22	270	1	75	181	10	7 610733 238255
PB 304.2	27	290	2	90	295	10	7 610733 238262
PB 304.3	32	320	3	100	442	10	7 610733 238279
PB 304.4	35	330	4	105	530	10	7 610733 238286
PB 304.5	40	355	5	110	740	10	7 610733 238293
PB 304.6	50	385	6	110	1140	6	7 610733 238309

PB 305 Combined engineer's hammer and soft mallet
 Dead-blow, handle made from premium fiberglass material
 Cushioning the recoil by weights in the mallet body
 - allows full and precise strikes

Martillo combinado de bola con cabeza plástica antirebote
 mango de fibra de vidrio de primera calidad
 Amortiguación del rebote mediante lastres en la cabeza del martillo
 - golpes fuertes y precisos



PB 305.1	270	1	75	259	10	7 610733 254743
PB 305.2	290	2	90	359	10	7 610733 254750
PB 305.3	320	3	100	547	10	7 610733 254767
PB 305.4	330	4	105	646	10	7 610733 254774
PB 305.5	355	5	110	824	10	7 610733 254781
PB 305.6	385	6	110	1298	6	7 610733 254798