

PB E6 100 PrecisionBits for slotted screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")
 PrecisionBits para tornillos de ranura, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.100/1	0.5	3.5	50	24	8	10	7 610733 206995
PB E6.100/2	0.6	4	50	24	8	10	7 610733 019113
PB E6.100/3	0.8	5.5	50	24	10	10	7 610733 019120
PB E6.100/4	1	6.25	50	24	11	10	7 610733 019137
PB E6.100/5	1.2	8	50	24	14	10	7 610733 019144
PB E6.100/6	1.6	10	50	24	18	10	7 610733 019151

PB E6 106 PrecisionBits for slotted screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")
 PrecisionBits para tornillos de ranura, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.106/1	0.6	3	75	50	11	10	7 610733 008261
PB E6.106/2	0.8	4	75	50	11	10	7 610733 008278
PB E6.106/3	1	5	75	50	11	10	7 610733 008285

PB E6 190 PrecisionBits for Phillips screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")
 PrecisionBits para tornillos Phillips, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.190/0	0	4	50	24	9	10	7 610733 207008
PB E6.190/1	1	5	50	24	9	10	7 610733 019168
PB E6.190/2	2	6	50	24	10	10	7 610733 019175
PB E6.190/3	3	6.25	50	24	11	10	7 610733 019182

PB E6L 190 PrecisionBits for Phillips screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")
 PrecisionBits para tornillos Phillips, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6L.190/1	1	5	95	70	16	10	7 610733 207015
PB E6L.190/2	2	6	95	70	21	10	7 610733 207022
PB E6L.190/3	3	6.25	95	70	31	10	7 610733 207039

PB E6 192 PrecisionBits for Pozidriv screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")

PrecisionBits para tornillos Pozidriv, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.192/0	0	4	50	24	9	10	7 610733 207046
PB E6.192/1	1	5	50	24	9	10	7 610733 019199
PB E6.192/2	2	6	50	24	10	10	7 610733 019205
PB E6.192/3	3	6.25	50	24	11	10	7 610733 019212

PB E6L 192 PrecisionBits for Pozidriv screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")

PrecisionBits para tornillos Pozidriv, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6L.192/1	1	5	95	70	16	10	7 610733 207053
PB E6L.192/2	2	6	95	70	21	10	7 610733 207060
PB E6L.192/3	3	6.25	95	70	31	10	7 610733 207077

PB E6 400 PrecisionBits for Torx® screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")

PrecisionBits para tornillos Torx®, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.400/1-50	1	50	24	7	10	7 610733 258000
PB E6.400/2-50	2	50	24	7	10	7 610733 258017
PB E6.400/3-50	3	50	24	7	10	7 610733 258024
PB E6.400/4-50	4	50	24	7	10	7 610733 258031
PB E6.400/5-50	5	50	24	8	10	7 610733 207084
PB E6.400/6-50	6	50	24	8	10	7 610733 207091
PB E6.400/7-50	7	50	24	8	10	7 610733 031559
PB E6.400/8-50	8	50	24	8	10	7 610733 031566
PB E6.400/9-50	9	50	24	8	10	7 610733 031573
PB E6.400/10-50	10	50	24	8	10	7 610733 031580
PB E6.400/15-50	15	50	24	9	10	7 610733 031597
PB E6.400/20-50	20	50	24	9	10	7 610733 031603
PB E6.400/25-50	25	50	24	10	10	7 610733 031610
PB E6.400/27-50	27	50	24	11	10	7 610733 207107
PB E6.400/30-50	30	50	24	11	10	7 610733 031627
PB E6.400/40-50	40	50	24	13	10	7 610733 031634

PB E6L 400
PrecisionBits for Torx® screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")
PrecisionBits para tornillos Torx®, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")


PB E6L.400/6-95	6	95	70	10	10	7 610733 258048
PB E6L.400/6-150	6	150	125	13	10	7 610733 258055
PB E6L.400/8-95	8	95	70	12	10	7 610733 258062
PB E6L.400/8-150	8	150	125	16	10	7 610733 258079
PB E6L.400/9-95	9	95	70	12	10	7 610733 258086
PB E6L.400/9-150	9	150	125	16	10	7 610733 258093
PB E6L.400/10-95	10	95	70	12	10	7 610733 223855
PB E6L.400/10-150	10	150	125	18	10	7 610733 258109
PB E6L.400/15-95	15	95	70	12	10	7 610733 223862
PB E6L.400/15-150	15	150	125	18	10	7 610733 258116
PB E6L.400/20-95	20	95	70	15	10	7 610733 223879
PB E6L.400/20-150	20	150	125	22	10	7 610733 258123
PB E6L.400/25-95	25	95	70	17	10	7 610733 223886
PB E6L.400/25-150	25	150	125	25	10	7 610733 258130
PB E6L.400/27-95	27	95	70	19	10	7 610733 258147
PB E6L.400/27-150	27	150	125	29	10	7 610733 258154
PB E6L.400/30-95	30	95	70	22	10	7 610733 223893
PB E6L.400/30-150	30	150	125	34	10	7 610733 258161
PB E6L.400/40-95	40	95	70	25	10	7 610733 223909
PB E6L.400/40-150	40	150	125	40	10	7 610733 258178

PB E6 401
PrecisionBits for Torx Plus® screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")
PrecisionBits para tornillos Torx Plus®, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")


PB E6.401/5	50	24	8	10	7 610733 207114
PB E6.401/6	50	24	8	10	7 610733 207121
PB E6.401/7	50	24	8	10	7 610733 207138
PB E6.401/8	50	24	8	10	7 610733 207145
PB E6.401/9	50	24	8	10	7 610733 207152
PB E6.401/10	50	24	9	10	7 610733 207169
PB E6.401/15	50	24	9	10	7 610733 207176
PB E6.401/20	50	24	9	10	7 610733 207183
PB E6.401/25	50	24	10	10	7 610733 207190
PB E6.401/27	50	24	11	10	7 610733 207206
PB E6.401/30	50	24	11	10	7 610733 207213
PB E6.401/40	50	24	13	10	7 610733 207220

PB E6 210 PrecisionBits for hexagon socket screws, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")

PrecisionBits para tornillos con hexágono interior, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.210/1,5	1,5	50	24	7	10	7 610733 093199
PB E6.210/2	2	50	24	8	10	7 610733 246038
PB E6.210/2,5	2,5	50	24	9	10	7 610733 019229
PB E6.210/3	3	50	24	9	10	7 610733 019236
PB E6.210/4	4	50	24	10	10	7 610733 019243
PB E6.210/5	5	50	24	11	10	7 610733 019250
PB E6.210/6	6	50	24	13	10	7 610733 019267
PB E6.210/8	8	50	24	17	10	7 610733 019274
PB E6.210/10	10	50	24	22	10	7 610733 019281

PB E6 180 PrecisionBits for mixed screws Pozidriv / slotted, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")

PrecisionBits para tornillos combinados ranura/Pozidriv, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.180/1	1	0.7	4	4	50	24	10	7 610733 092475
PB E6.180/2	2	1	6	6	50	24	11	7 610733 092482

PB E6L 180 PrecisionBits for mixed screws Pozidriv / slotted, external hexagon according to DIN ISO 1173 shape E 6,3 (1/4")

PrecisionBits para tornillos combinados ranura/Pozidriv, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6L.180/1	0.7	4	4	95	70	13	7 610733 093229
PB E6L.180/2	1	6	6	95	70	20	7 610733 093236

PB E6 200

Socket wrench bits, external hexagon according to DIN ISO 1173 shape E 6.3 (1/4")

Puntas de llave de vaso para tornillos hexagonales, hexágono exterior según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.200/5	2,5	60	16	10	7 610733 060481
PB E6.200/5,5	3	60	16	10	7 610733 060498
PB E6.200/6	3,5	60	17	10	7 610733 060504
PB E6.200/7	4	60	19	10	7 610733 060511
PB E6.200/8	5	60	20	10	7 610733 060528
PB E6.200/9		60	23	10	7 610733 060535
PB E6.200/10	6	60	27	10	7 610733 060542
PB E6.200/11	7	60	30	10	7 610733 060559
PB E6.200/12		60	33	10	7 610733 060566
PB E6.200/13	8	60	38	10	7 610733 060573

PB E6 200 M

Socket wrench bits, with magnet, external hexagon according to DIN ISO 1173 shape E 6.3 (1/4")

Puntas de llave de vaso para tornillos hexagonales, con imán, hexágono ext. según DIN ISO 1173, forma E 6,3 (1/4")



PB E6.200/5 M	2,5	60	17	10	7 610733 060603
PB E6.200/5,5 M	3	60	18	10	7 610733 060610
PB E6.200/6 M	3,5	60	18	10	7 610733 060627
PB E6.200/7 M	4	60	21	10	7 610733 060634
PB E6.200/8 M	5	60	23	10	7 610733 060641
PB E6.200/9 M		60	26	10	7 610733 060658
PB E6.200/10 M	6	60	32	10	7 610733 060665
PB E6.200/11 M	7	60	37	10	7 610733 060672
PB E6.200/12 M		60	41	10	7 610733 060689
PB E6.200/13 M	8	60	48	10	7 610733 060696