knitter-switch

Product-Change Notification

Affected Product:

LD 46-24, LD 46 S -24

Effective Date:

immediately

Details:

Due to obsolescence of semiconductor, a modification of the part became unavoidable. The appearance differs slightly in mounted condition.

Therefore we do not recommend a mix of old and new parts in one and the same panel.



LD 46-24 old drawing 303732

LD 46-24 new drawing 303731

Details are shown in the attached data-sheets. Electro-optical data comparison:


	<u>old</u>	new
Power dissipation, max. [mW]	125	105
Forward voltage, typ. [V]	2.1	2.2
Forward current, max. [mA]	20	25
Peak emission wave length, typ. [nm]	555	565
Luminous Intensity at 10 mA, typ. (mcd)	12	n.a.
Luminous efficiency [lm/W]	n.a.	660
Reverse voltage [V]	4	5
Reverse current [µA]	100	10
Operating temperature [°C]	-30/+85	-45/+85


knitter-switch, November 2016

Oliver Kluj

Technical Director

knitter-switch






Orde	ring code	Housing	LED color (operation voltage 24V DC)
LI	D 36	brass, chromium plated	red
LI	D 46	brass, chromium plated	green
LI	D 66	brass, chromium plated	yellow
LI	D 36 S	brass, black, matt finish	red
LI	D 46 S	brass, black, matt finish	green
LI	D 66 S	brass, black, matt finish	yellow

Compliance: RohS II (2011/65/EU)

-	compliance. Note in (2017/06/20)								
ı	Tolerances:			Date	Name				
ı				11/16	dr				\circ
ı						LU	LD x6-24_LD x6 S-24		
ı									
ı									
ı							00.07	00	Page
ı				kni	tter-s	witch	30 37	32	rage
ı							000.	-	1/1
	Modifications	Date	Name						

knitter-switch





x	Case				
(empty)	brass, chromium plated				
S	brass, chromium black plated				

Specifications:

Power dissipation: 10

105mW

Forward voltage: Forward current: Luminous efficiency: 2.2V; max. 2.5V 25mA max.

Peak emission wavelength: 565nm Reverse voltage: 5V

660lm/W 565nm

Reverse current: Operating temperature: 10µA -45°C to +85°C

Operation voltage: 24V DC (by built-in resistor)

Compliance: RohS II (2011/65/EU)

Compliance. Notion (2017/03/20)									
Tolerances: ±0.25mm			Date	Name					
		11/16	dr	LD 40 04					
					≝ LD 46 x-24				
					1		· – ·		
					_	00.07	~ 4	Page	
			kni	tter-s	witch	30 37	31	rage	
						00 07 01		1/1	
Modifications	Date	Name							