

NELCO CONTACT AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se





PCT-0150-030-BL-100

Cable Tie, 150x3.2mm, Blue Plastic Barb

Cable ties in high industrial quality with rounded edges to prevent cable damage.Inclined tip to indicate usage direction and quick installation time.Material: Polyamid 6.6Temp range: -40 degrees Celsius to +85 degrees Celsius Flammability rating: UL94-V2



Product Properties:

Model	Internal toothing
Material quality	Polyamide (PA)
Band closure	Plastic lip/-cam
UV-stable acc. ASTM D6779	No
Transparent	No
Solvable fastener	No
Text strip	None
Type of fastening	None
Colour	Blue
Surface protection	Untreated
Material	Plastic
Halogen free	Yes
Inflammability class of insulation material according to with UL94	V2
Operating temperature	-40-85 °C
Max. tensile force	180 N

Dimensions:

Unit pcs

Length belt/tape/tie	150 mm
Band width	3.3 mm
Max. bundle diameter	38 mm
Max. tensile force	180 N
MOQ	100 .

Approvals:

Approved according to CE	Yes
Approved according to UR	Yes
With approval according to UL	Yes
Inflammability class of insulation material according to with UL94	V2

Compliance:

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (233 Subs. Jan 2023)
SCIP	Not Applicable

Other information:

Trademark	NEMIQ
ETIM-Class	EC000046 - Cable tie
ETIM-Release	7.0
Product Group	Standard Cable ties
Alternative SKU	PCT-0150-030-BL-100

Logistic information:

Barcode	733117640057
Country of origin	TW
Item status	Stock item, normally in stock with reservation for in between sales., Non Stock Item, can be on stock but is not a regular stock item.
Stock code	PCT-0150-030-BL-100
Taric code	39269097
Unit	pcs
MOQ	100 .