



PRIME COMPUTER

PrimeMini Pro

Specification

PC form factor	Ultra Slim	
Colour	Black	
Number of processors	1	
Processor family	Core i5 5th Gen	Core i3 5th Gen
Processor type	Intel Core i5-5300U vPro	Intel Core i3-5010U
Intel VPro	Yes	No
Processor clock frequency	2.3 GHz	2.1 GHz
Max turbo clock frequency	2.9 GHz	
Max TDP	15 W	
Number of processor cores	2	
Number of threads	4	
Cache	3MB SmartCache	
RAM	4GB, 8GB, 16GB, 32GB DDR3L-1600MHz	
RAM form factor	SODIMM 204	
Number of RAM slots	2	
SSD capacity m.2	120GB, 250GB, 500GB, 1TB Samsung EVO 850	
Optional: 2.5" SSD SATA	250GB, 500GB, 1TB, 2TB, 4TB Samsung EVO 850 or RS232	
Wi-Fi & Bluetooth	Optional: Intel Dual Band Wireless-AC 7265	
Graphics card brand	Intel	
Graphics card type	On Board	
Graphics card model	Intel HD Graphics 5500	
Operating system	Windows	
Supported operating systems	Win 10, Win 8.1, Win 7, Windows Server 2012 R2 / 2016, Linux Mint / Ubuntu / Fedora / OpenSUSE / Debian / ESXi (driver required)	
Operating system architecture	64-bit	
Multilingual	Yes	
Languages	DE, FR, IT, EN	
Dimensions	W: 16,4 cm, H: 4,7 cm, L: 11,2 cm	
Weight	0,98 kg	
Video connections	2x Mini-DP 1.2	
Number of ethernet ports	1	
Ethernet speed	10/100/1000 Mbit/s	
Wi-Fi standard	802.11a, 802.11ac, 802.11b, 802.11g, 802.11n	
Wi-Fi transfer rate (max)	867 Mbit/s	
Front panel connections	2x USB3.0, 1x Microphone / headphone combo	
Rear panel connections	2x USB3.0, 1x RJ45/LAN port, 2x MiniDP, 1x DC, 2x Wi-Fi antenna, optional: RS232	
Infrared	Optional (not available with 2.5" SDD)	
RS232	No	