

Product data sheet

Specifications



Power Distribution Panel, Single Input Main Input Breaker, 6U, 230/400V, Black, 438x265x460mm

PDPMIB1N-40

Overview

Presentation	A set of power distribution panels specifically designed to be rack mounted and support EcoStruxure Row Data Center solutions. This power distribution panel supports a single input main input breaker.
Lead time	Usually Ships within 4 Weeks

Main

Main Input Voltage	230 V AC
Main Output Voltage	230/400 V
Other Output Voltage	230/400 V
Output connector type	Terminal block 5-wire (3P + N + E) 2

Physical

Colour	Black and silver
Height	265 mm
Width	482.6 mm
Depth	502 mm
Net weight	17.5 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Load capacity	40 kVA
----------------------	--------

Output

Protection type	Circuit breaker
------------------------	-----------------

Conformance

Standards	CE
------------------	----

Environmental

Operating altitude	0...1000 m
---------------------------	------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	39.5 cm
Package 1 Width	58.5 cm
Package 1 Length	66 cm
Package 1 Weight	23.8 kg
Pallet unit layers	2
Pallet layers	2

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	Two-Year Factory Warranty
----------	---------------------------

Recommended replacement(s)