

Product data sheet

Specifications



Power Distribution Panel, Dual Input Main Input Breaker, 6U, 230/400V, Black, 438x265x460mm

PDPMIB2N-20

Overview

Presentation	A set of power distribution panels specifically designed to be rack mounted and support EcoStruxure Row Data Center solutions. This power distribution panel supports a dual input main input breaker.
Lead time	Usually Ships within 4 Weeks

Main

Main Input Voltage	230 V AC
Main Output Voltage	230/400 V
Other Output Voltage	230/400 V
Output connector type	Terminal block 5 wire (3P + N + E) 2

Physical

Colour	Black and silver
Height	265 mm
Width	482.6 mm
Depth	502 mm
Net weight	17.8 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Input current limits	40 A
Load capacity	20 kVA

Output

Protection type	Circuit breaker
------------------------	-----------------

Conformance

Standards	CE
------------------	----

Environmental

Operating altitude	0...1000 m
--------------------	------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	39.5 cm
------------------	---------

Package 1 Width	58.5 cm
-----------------	---------

Package 1 Length	66 cm
------------------	-------

Package 1 Weight	24 kg
------------------	-------

Pallet unit layers	2
--------------------	---

Pallet layers	2
---------------	---

Offer Sustainability

REACH Regulation	REACH Declaration
------------------	-----------------------------------

REACH free of SVHC	Yes
--------------------	-----

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Toxic heavy metal free	Yes
------------------------	-----

Mercury free	Yes
--------------	-----

China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
-----------------------	---

RoHS exemption information	Yes
----------------------------	---------------------

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

Contractual warranty

Warranty	Two-Year Factory Warranty
----------	---------------------------

Recommended replacement(s)