

Product datasheet

Specifications



Power Distribution Panel, Supporting 2N UPS, 4U, 230/400V, Black, 438x175x460mm

PDPUPS2N-20

Overview

Presentation	A set of power distribution panels specifically designed to be rack mounted and support EcoStruxure Row Data Center solutions. This power distribution panel supports a 2N redundancy UPS.
Lead time	Usually Ships within 4 Weeks

Main

Main Input Voltage	230 V AC
Main Output Voltage	230/400 V
Other Output Voltage	230/400 V
Output connector type	Terminal block 5-wire (3P + N + E) 2

Physical

Colour	Black and silver
Height	175 mm
Width	482.6 mm
Depth	560 mm
Net weight	16.2 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Input current limits	40 A
Load capacity	20 kVA

Output

Protection type	Circuit breaker
------------------------	-----------------

Conformance

Standards	CE
------------------	----

Environmental

Operating altitude 0...1000 m

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 27.5 cm

Package 1 Width 58.5 cm

Package 1 Length 77 cm

Package 1 Weight 22 kg

Pallet unit layers 2

Pallet layers 3

Offer Sustainability

REACH Regulation [REACH Declaration](#)

REACH free of SVHC Yes

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Toxic heavy metal free Yes

Mercury free Yes

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

RoHS exemption information [Yes](#)

WEEE The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty Two-Year Factory Warranty

Recommended replacement(s)