


4-port PCI Express RS232 Serial Adapter Card - PCIe RS232 Serial Host Controller Card - PCIe to Serial DB9 Card - 16950 UART - Expansion Card - Windows, macOS, Linux

**Product ID:** PEX4S953



This PCI Express RS232 serial adapter card lets you add four RS232 (DB9) serial ports to your computer through a PCI Express (PCIe) slot, as if they were native serial ports. The 4 port PCIe serial card enables you to interact with serial devices, such as card readers, printers, PIN pads, and modems, at speeds of up to 921.6Kbps.

With broad OS support, including for Windows and Linux, this multiport PCI E serial card is easy to integrate into mixed environments. The card comes pre-configured with a full-sized bracket, and includes an optional low-profile bracket, so installation is easy regardless of the case form factor. This expansion card is a direct replacement for PEX4S952.

This PCIe to serial adapter supports the following features:

- Industry standard 16950 UART compatible
- Supports max baud rate of up-to 921.6Kbps
- Provides 5/12V power output on Pin 9 when external power is connected
- 256-byte depth FIFO cache per transmitter and receiver
- Supports 9, 8, 7, 6, 5 data bits (one per port)
- Asix AX99100 chipset
- Base PCI Express 1.1 compliant

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

PEX4S953 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect to automated self-service kiosks or ATM machines
- Connect in retail POS applications
- Install in home or office workstations
- Connect serial printers and other legacy devices to modern computers

### Features

- **4 PORT SERIAL CARD:** Serial controller card w/ 16950 UART based on ASIX AX99100, allows 4x DB9 ports w/bi-directional RS232 speeds up to 921.6Kbps per port, available 256 byte FIFO buffer
- **OPTIONAL CONFIGURABLE POWER:** PCIe multiport serial card provides 12v, 5v, or none through pin 9 w/up to 2A total; Each of the 4 ports are individually configurable; DB44 to 4x DB9 breakout cable incl
- **STANDARD PROFILE & LOW PROFILE BRACKET:** PCI Express RS232 serial adapter card has standard bracket pre-installed & 1x low profile bracket incl for versatile install; Supports Windows XP and up & Linux
- **VERSATILE APPLICATIONS:** For standard profile desktop/servers with uses in point of sale terminals, PLCs, control/automation in factories, scientific sensors, medical equipment, scanners, oscilloscope
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; PCI-e RS232 Serial expansion card is backed for life by StarTech.com, incl. free 24/5 North America based multi-lingual tech support

---

#### Prominence

Warranty	Lifetime
Description CDW 75 - 1st Line	StarTech.com 4-port PCI Express RS232 Serial Adapter Card - PCIe Serial DB9

---

#### Hardware

Ports	4
Interface	Serial
Bus Type	mini PCI Express
Card Type	Low Profile (SP bracket incl.)

Port Style Integrated on Card

Chipset ID Asix AX99100

**Performance**

Serial Protocol RS-232

Max Baud Rate 921.6 Kbps

Data Bits 5, 6, 7, 8, 9

FIFO 256 Bytes

Flow Control None, Xon/Xoff, RTS/CTS

Parity None, Odd, Even, Space, Mark

Stop Bits 1, 1.5, 2

MTBF 214,358 hours

**Connector(s)**

Connector Type(s) PCI Express x1

Internal Ports LP4 (4 pin; Large Drive Power)

External Ports DB-9 (9 pin, D-Sub)

**Software**

OS Compatibility Windows 7, 8, 8.1, 10  
Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016  
Linux 2.4.x to 2.6.x <i>LTS Versions only</i>

Microsoft WHQL Certified Yes

**Special Notes / Requirements**

Note Selectable power output on pin 9 of the serial port

**Environmental**

Operating Temperature -10C to 80C (14F to 176F)

Storage Temperature -20C to 100C (-4F to 212F)

Humidity 5~85% RH



**Physical Characteristics**

Material	Steel
Cable Length	11.8 in [30 cm]
Product Length	3.0 in [75.0 mm]
Product Width	2.5 in [63.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	1.8 oz [50.0 g]

**Packaging Information**

Package Length	8.3 in [21.0 cm]
Package Width	5.9 in [15.0 cm]
Package Height	2.0 in [50.0 mm]
Shipping (Package) Weight	13.1 oz [371.0 g]

**What's in the Box**

Included in Package	4 Port PCI Express Serial Card
	Full Profile Bracket (Installed)
	Low Profile Bracket
	12 in [30 cm] DB44 to DB9 Break-out Cable
	Quick Start Guide

***\*Product appearance and specifications are subject to change without notice.***

